

Алматы (7273)495-231  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922) 49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Ижевск (3412)26-03-58  
Иваново (4932)77-34-06  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Киргизия (996)312-96-26-47

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Ноябрьск (3496)41-32-12  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37

Россия (495)268-04-70

Пермь (342)205-81-47  
Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Саранск (8342)22-96-24  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сыктывкар (8212)25-95-17  
Сургут (3462)77-98-35  
Тамбов (4752)50-40-97

Казахстан (772)734-952-31

Тверь (4822)63-31-35  
Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Улан-Удэ (3012)59-97-51  
Ульяновск (8422)24-23-59  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

<https://euroclinic.nt-rt.ru> || [ecy@nt-rt.ru](mailto:ecy@nt-rt.ru)

# ЛОР-комбайн Otocompact Professional EVO



## Description

ENT **Top Range** workstation with a state-of-the-art integrated technology and elegant and unique design.

Solid case in steel painted with epoxy powders in color silver grey or white RAL 9003.

Transparent gloss layer for easy cleaning and better protection against external agents (optional).

Such treatment grants a long durability in time and high resistance of the colors to the light.

The case is also mobile on 6 antistatic castors with brakes that help the operator in the floor cleaning and sanification as well as in the easy positioning anywhere in the outpatient room.

Working top in tempered glass. linear surface for an easier disinfection against proliferation of bacteria.

### **Standard Applications:**

- Color and adjustable touch screen 7"
- Wireless control of the motorized movement of the combined chair, if present
- Working top in tempered and colored crystal ( at choice among 20 nuances)
- Motorized drawers in metal, epoxy painted or in tempered and colored glass ( at choice among 20 nuances)
- Powered suction system (50 lt/min or 70 lt/min) complete with suction jar (1 lt. capacity)
- Hydrophobic filter
- Kit of stainless steel suction canulas
- Ear funnel
- Insufflation system with digital manometer
- Ear washing syringe with fixed temperature 37°
- Mirror warmer
- Integrated 3-channel LED light source - 5.500°K 200 L with f.o. cables
- Integrated LED light source with handpiece for direct connection to endoscopes
- Nr. 8 integrated endoscope supports in Plexiglass
- Nr. 2 supports for headlamp

### **Optional Application:**

- Application of second suction system
- Application of single-use suction jar (1 or 2 lt. capacity)
- Automatic discharge system
- Automatic rinsing system for suction tube
- Connection to the water main
- Application of kit for medicaments, available up to 6 medicament bottles
- Warming system for 2 endoscope supports
- Pole support for microscope with articulated arm for monitor
- Video-Endoscopy system
- Microscope
- Video Nystagmoscope
- Rhinomanometer

## **Details**

---



### **Touch screen display 7"**

Color touch screen display 7", on instruments tablet with articulated arm , for instruments control and remote control of the combined treatment chair (if 3-4 motors with radiofrequency predisposition)



## Instruments tablet

Instruments tablet housing Suction system, Insufflator with Politzer olives, Ear Washing system and Compressed air system for medicaments (optional)



## Head-lamp support

Hang your tools in a comfortable and fast way



## Motorized drawers

Electrical Drawers with servo-drive system complete with Inox trays for instruments ( automatic opening and closing system without handles)



## UV Germicide compartment

UV germicide compartment activated by touch screen and automatic switch OFF at the drawer's opening



### **Radiofrequency module WIFI**

Radiofrequency module for the control on wireless modality of 3/4 motors chair (if combined).



### **In-built holders for endoscopes**

Integrated Endoscopes Supports (8 tubes: n.2 for flexible endoscopes - clean and dirty / 6 for rigid endoscopes - clean and dirty)



### **Larynx Mirror warmer**

Mirror warmer with time setting by touch screen (10-120 sec)



### **Pole support for ZEISS® Microscope (optional)**

# Standard Applications

---



## Kit of stainless steel suction cannulas

Stain Steel suction cannulas



## Lateral service compartment

With secretion jar and water tank for washing syringe



## Powered suction system

With multi-use suction jar and ear funnel



## LED light HANDLE

Integrated LED light HANDLE for direct connection to endoscopes or laryngoscopes and with high performance temperature of 5500° Kelvin/200 Lumen. Automatic activation and brightness intensity adjustment by touch screen.


## Adjustment of LED light intensity

Visualization and adjustment of LED light sources intensity by Touch Screen control panel

## LED light source with double or triple connection

Integrated Led Light source with triple outlet and n.3 fiber optic cables. Colour temperature of 5.500°K/200 L. Brightness intensity regulation by Touch Screen Control Panel.

# Technical details



| NAME                 | VALUE                  |
|----------------------|------------------------|
| Power supply tension | 220/240 V(110/115 VAC) |
| Frequency            | 50/60 Hz               |

Absorbed power (MAX  
maximum configuration) 1550 VA

Weight 180 Kg

Maximum number of  
instruments 4

Insufflator air flow 26 l/m (variation up to 250 Kpa)

Washing stringe capacity 350 cc/min (at 2 Bar)

Nominal suction (oil motor) -86 Kpa (-650 mm Hg 50 L/min)

Power supply fuses F1, F2 = 6,3 A T

Fuse external Plug F3 = 4 A T

Алматы (7273)495-231  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922) 49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Ижевск (3412)26-03-58  
Иваново (4932)77-34-06  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Киргизия (996)312-96-26-47

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижегород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Ноябрьск (3496)41-32-12  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37

Россия (495)268-04-70

Пермь (342)205-81-47  
Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Саранск (8342)22-96-24  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сыктывкар (8212)25-95-17  
Сургут (3462)77-98-35  
Тамбов (4752)50-40-97

Казахстан (772)734-952-31

Тверь (4822)63-31-35  
Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Улан-Удэ (3012)59-97-51  
Ульяновск (8422)24-23-59  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

<https://euroclinic.nt-rt.ru> || [ecy@nt-rt.ru](mailto:ecy@nt-rt.ru)